ENTER THE STATE OF


OKAPA

ANATOMY:

THERE ARE 8 MODULAR PIECES TO EVERY OKAPA BOTTLE BECAUSE AN OKAPA BOTTLE IS BUILT TO BE QUICK AND/OR DEEP CLEANED IN THE MOST HYGENIC WAY

- SPOUT MADE OF PREMIUM SWISS GRILAMID TR-90 ALSO USED IN THE MEDICAL FIELD
- SILICONE SAFETY GASKET FOR SPOUT
- 3. SILICONE SAFETY KNOB INSERT FOR TOP CAP
- 4. TOP CAP SECTION MADE OF PREMIUM SWISS GRILAMID TR-90 (ALSO USED IN THE MEDICAL FIELD) WITH OPEN AND CLOSING STEEL MECHANISM & SPOUT RELEASE BUTTON
 - SNAP IN SILICONE SAFETY RING FOR TOP CAP
- 6. GERMAN MADE PREMIUM BOROSILICATE GLASS 3.3 ALSO USED IN THE MEDICAL FIELD (MICROWAVE-SAFE)
- 7. EXTRUDED, PERFORATED AND ANODIZED ALUMINIUM SHELL
 - BOTTOM SILICONE SNAP INSERT FOR SAFETY SHOCK ABSORPTION AND GLASS POP IN FUNCTION.

ALL FOUR SILICONE PARTS ARE ESSENTIAL FOR LEAK PROOF, SAFETY AND PERFORMANCE!




ALUMINUM SHELL


YOUR OKAPA BOTTLE:

YOUR OKAPA BOTTLE USES PREMIUM MATERIALS ALSO USED IN THE MEDICAL FIELD BECAUSE AN OKAPA BOTTLE IS BUILT FOR HYGIENE // YOUR OKAPA BOTTLE HAS A SNAP-IN SAFETY SYSTEM BECAUSE AN OKAPA BOTTLE IS BUILT FOR THE RIDE // YOUR OKAPA BOTTLE USES 100% RECYCLABLE MATERIALS BECAUSE AN OKAPA BOTTLE IS BUILT FOR THE FUTURE // YOUR OKAPA BOTTLE IS DESIGNED TO BE SIMPLE BECAUSE YOUR OKAPA BOTTLE IS MEANT TO BE USED // YOUR OKAPA BOTTLE IS THERMAL SHOCK RESISTANT TO EXTREME HOT AND COLD // THE GLASS CARAFE OF YOUR OKAPA BOTTLE IS BUILT FOR THE SENSES BECAUSE OKAPA BELIEVES IN ADDICTIVE HYDRATION.


LOCKING & OPENING:



FILLING:



3 PIECE QUICK CLEAN:





O-FIECE FORE FAMATIC CLEAN.

